



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



49322INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 39.523
GD RADIUS : 104.333
SCALE BAR : 400


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49322INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 239.7807 μm
DIFFRACTION LIMITED RANGE: 5.999 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT



TRANSVERSE RAY FAN PLOT


49322INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 500.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

49322INK
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF



EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

EO Edmund
optics | worldwide

www.edmundoptics.com