




NOTES:

1. SUBSTRATE  
BOROFLOAT®
2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)  
T(AVG) <1.0% @ 535 - 565nm  
T(AVG) >80% @ 380 - 470nm  
T(AVG) >80% @ 655 - 750nm



3. CUT AND SEAM

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION 	TITLE	50 x 50 MAGENTA DICHROIC FILTER	
SURFACE QUALITY	80-50	80-50		DWG NO	39913	SHEET 1 OF 1
CLEAR APERTURE	≥85 %	≥85 %		ALL DIMS IN	mm	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				