




NOTES:

- 1. SUBSTRATE:
BOROFLOAT®
- 2. COATING SPECIFICATION:
S1: Protected Gold (700-10000nm)
R(AVG) >96% @ 700 - 2000nm
R(AVG) >96% @ 2000 - 10,000nm



3. FINE GROUND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

			 Edmund Optics®			
SHAPE	S1 PLANO	S2 PLANO		TITLE	25mm Dia. Protected Gold, λ/4 Mirror	
SURFACE QUALITY	60-40	COMMERCIAL POLISH				
CLEAR APERTURE	Ø21.25	N/A				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		DWG NO	45606	SHEET 1 OF 1
			ALL DIMS IN	mm		