




NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. ROHS COMPLIANT
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
S1: Ravg >98% @ 750 - 1100nm
S2: NONE
- 4. FINE GRIND SURFACE




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
ANGLE TOL. (arcmin)	±2	±2
SURFACE QUALITY	40-20	40-20
SURFACE FLATNESS	λ/8	λ/8
CLEAR APERTURE	90%	90%
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN mm

**Edmund Optics®**

TITLE	15mm, 750 - 1100nm DIELECTRIC COATED, N-BK7 RIGHT ANGLE MIRROR
DWG NO	87399
SHEET	1 OF 1