



- NOTES:
- 1. SUBSTRATE:
B270
 - 2. COATING



S1: NONE
S2: NONE
S3: NONE
 - 3. EDGES: FINE GROUND



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	S3
SHAPE	PLANO	PLANO	PARABOLIC
RADIUS	∞	∞	ASPHERIC
SURFACE QUALITY	80-50	80-50	(80-50)
CLEAR APERTURE	$\phi 4.85$	$\phi 2.25$	N/A
BEVEL MAX	PROTECTIVE AS NEEDED		NONE

THIRD ANGLE PROJECTION 		 Edmund Optics®	
TITLE		45°, 2.5mm OUTPUT DIA., COMPOUND PARABOLIC CONCENTRATOR	
ALL DIMS IN	mm	DWG NO	65443
			SHEET 1 OF 1