

NOTES:



1. SUBSTRATE MATERIAL:  
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Gold  
R(avg) >96% @ 700 - 2000  
R(avg) >96% @ 2000 - 10000nm

S2: NONE

3. FINE GROUND SURFACE

4. RoHS COMPLIANT



SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	CONCAVE	CONVEX
RADIUS	20mm	20mm
APERTURE	f/0.4	N/A
EFFECTIVE FOCAL LENGTH	10mm	N/A
FOCAL LENGTH TOLERANCE	±2%	N/A
SURFACE QUALITY	80-50	N/A

THIRD ANGLE PROJECTION

ALL DIMS IN mm

**Edmund Optics®**

TITLE	25mm Dia. x 10mm FL Protected Gold, Concave Mirror		
DWG NO	43834	SHEET 1 OF 1	