

NOTES:



1. SUBSTRATE MATERIAL:
B270

3. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: NONE

4.  EDGES FINE GROUND

5. RoHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

GROOVES/mm	HeNe DIFFRACTED ORDER TYPICAL DISTRIBUTION @ 632.8nm (%)				
	-2	-1	0	+1	+2
80	5	25	25	25	5
	S1		S2		
SHAPE	PLANO		PLANO		
GROVE DENSITY (GROOVES/mm)	80		N/A		
BEVEL	PROTECTIVE AS NEEDED		PROTECTIVE AS NEEDED		

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm



TITLE	80 GROOVES/mm, 25.0mm SQ, TRANSMISSION GRATING BEAMSPLITTER		
DWG NO	46070	SHEET	1 OF 1