







FOCAL LENGTH (EFL): 200 ±2
 BACK FOCAL LENGTH (BFL): 194,14

1 BLACKENED SURFACE


SURFACE A			SURFACE B		SURFACE C		
Øe 24			Øe 24 CEMENT: NOA 61 OR EQUIVALENT		Øe 24		
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 	 Edmund Optics® TITLE25mm Dia, x 200mm FL,, VIS 0, Inked, Achromatic Lens			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE25mm Dia, x 200mm FL,, VIS 0, Inked, Achromatic Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING							
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO47645INK	SHEET SIZE A4	SHEET 1 OF 3



1 AR COATING: VIS 0°
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI


LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 124,12±0,124 CX Øe 24 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-BK7 517/642	R 87,26±0,087 CX Øe 24 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 25mm Dia, x 200mm FL,, VIS 0, Inked, Achromatic Lens			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm					DWG NO 47645INK
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					SHEET SIZE A4			
INDICATIONS IN ACCORDANCE WITH ISO 10110			SHEET 2 OF 3					



- 1 AR COATING: VIS 0°
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 87,26±0,087 CV Øe 24 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-SF5 673/322	R 253,1±0,253 CX Øe 24 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE	25mm Dia, x 200mm FL,, VIS 0, Inked, Achromatic Lens		
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN:		mm	DWG NO	47645INK	SHEET SIZE A4
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				INDICATIONS IN ACCORDANCE WITH ISO 10110				