

NOTES:

1. MATERIAL: N-BK7 MOUNTED IN BLACK ANODIZED ALUMINUM

2. COATING (APPLY ACROSS COATING APERTURE):

S1 & S2: YAG-BBAR



R(ABS) < 0.25% 532nm @ 0° AOI

R(ABS) < 0.25% 1064nm @ 0° AOI

R(AVG) < 1.0% FROM 500 - 1100nm @ 0° AOI

3. RoHS: COMPLIANT


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	PLANO
RADIUS	62.02	INFINITY
SURFACE QUALITY	40-20	40-20
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EFL: 120.00mm		 Edmund Optics®	
BFL: 116.04mm			
 THIRD ANGLE PROJECTION		TITLE	120mm FL LASER FOCUSING SINGLET
ALL DIMS IN	mm	DWG NO	12321
			SHEET 1 OF 1