


► Technical Specification




Focal length	24.91 mm
Aperture Range	f/1.4 - f/22
Lens elements/Groups	13/12
Focusing Range	0.25m - ∞
Diameter of image field	43.4 mm
Flange focal distance	CA: 46.5mm, NI: 44mm
M.O.D	0.25m
Image ratio at MOD	1:5.1
Diameter max	$\Phi 83$
Filter Size	$\Phi 77.0\text{mm}$
Rotation angle of focusing ring($\text{inf}-\infty$)	130


Working distance	Magnification	W.D
	0.028	860.0mm
	0.066	360.0mm
	0.195	110.0mm

※ WD calculation



► Lens Dimension



► MTF Charts



► Relative Illuminance



► Relative Distortion

