

1. SUBSTRATE:
SCHOTT KG1




2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: NONE

3. FINE GRIND SURFACE

4. DENSITY (g/cm³) : 2.53
OPERATING TEMPERATURE (°C): 300 Maximum
REFLECTION FACTOR: 0.92



5. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2					SCHOTT KG1, 25mm Dia., 2mm Thick, Colored Glass Heat Absorbing Shortpass Filter	
SHAPE	PLANO	PLANO						
SURFACE QUALITY	60-40	60-40						
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	19320	SHEET 1 OF 1	