






NOTES:


1. GLASS SUBSTRATE: N-SF6
2. MOUNT MATERIAL: 416 STAINLESS STEEL
3. NUMERICAL APERTURE: 0.66
4. COATING
S1 & S2: NONE
5.  DIAMOND TURNED SURFACE
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION 		TITLE	25mm Dia., 0.66 NA, Uncoated, Mounted Precision Aspheric Lens		
SURFACE QUALITY	40-20	40-20			TITLE			
CLEAR APERTURE	Ø 22.50	Ø 22.50			TITLE			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	16845	SHEET 1 OF 1	