

LDR2-50RD2

Model name	LDR2-50RD2
LED color	Red
Input voltage	24VDC
Power consumption	3.1W max.
Weight	50g
Connector	SMR-03V-B
Polarity and signal	1: (+), 2: NC, 3: (-)

Third Angle Projection Units: mm

