

LDR2-70RD2

Model name	LDR2-70RD2
LED color	Red
Input voltage	24VDC
Power consumption	6.1W max.
Weight	110g
Connector	SMR-03V-B
Polarity and signal	1: (+), 2: NC, 3: (-)

Third Angle Projection Units: mm

