



NOTES:



- 1. SUBSTRATE MATERIAL: N-BK7
- 2. ROHS COMPLIANT
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: NONE
 - S2: Ravg >98% @ 450 - 2000nm
 - Ravg >98% @ 2000 - 10,000nm

4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO				
ANGLE TOL. (arcmin)	±2	±2				
SURFACE QUALITY	40-20	40-20				
SURFACE FLATNESS	λ/8	λ/8				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				
ALL DIMS IN			mm	TITLE	15mm, Protected Silver Coated, N-BK7 90° Specialty Mirror	
				DWG NO	21187	SHEET 1 OF 1