

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

4/3" Format Fixed Focal Length Lenses



- Up to 1", C-Mount Lens
- Less than 1.0% TV Distortion
- 12mm to 50mm Focal Length

Common Specifications

General

Product Family:	4/3" Format Fixed Focal Length Lenses
------------------------	---------------------------------------

Physical & Mechanical Properties

Iris Option:	Variable
---------------------	----------

Optical Properties

Maximum Image Circle (mm):	21.60
-----------------------------------	-------

Sensor

Maximum Sensor Format:	4/3"
-------------------------------	------

Pixel Size (µm):	5.00
-------------------------	------

Threading & Mounting

Mount:	C-Mount
---------------	---------

Technical Information

Products

Focal Length FL (mm)	Max. Sensor Format	Aperture (f/#)	Working Distance (mm)	Mount	Stock Number	Price	Buy
12.00	4/3"	f/2 - f/22	100 - ∞	C-Mount	#86-206	S\$3,024.00	Contact Us
16.00	4/3"	f/2 - f/22	100 - ∞	C-Mount	#86-207	S\$2,861.00	Contact Us
25.00	4/3"	f/2 - f/16	150 - ∞	C-Mount	#86-208	S\$2,502.00	Contact Us
35.00	4/3"	f/2 - f/16	200 - ∞	C-Mount	#86-209	S\$2,502.00	Contact Us
50.00	4/3"	f/2 - f/22	300 - ∞	C-Mount	#86-210	S\$2,502.00	1 In Stock



Copyright 2024, Edmund Optics Singapore Pte. Ltd, 18 Woodlands Loop #04-00, Singapore 738100

[PRIVACY POLICY](#) [COOKIE POLICY](#) [TERMS & CONDITIONS](#)

Phone: 1-800-363-1992 :

www.edmundoptics.com