

TECHSPEC® 0.15X MercuryTL™ Liquid Lens Telecentric Lens



0.15X MercuryTL™ Liquid Lens Telecentric Lens, #36-188



Stock **#36-188** 3-5 DAYS



1



S\$2,897.00

ADD TO CART

Qty 1+

S\$2,897.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length excluding Threads (mm):
186.70

Horizontal Field of View, 1/2" Sensor:
41.2mm

Filter Thread:
M62 x0.75 (Female)

Weight (g):
405

Horizontal Field of View, 1/3" Sensor: 30.9mm
Stock No. of Mounting Clamp: #56-871 Sold Separately
Note: MercuryTL™
Typical Telecentricity @ 588nm (°): <0.050
Typical Distortion @ 588nm (%): <0.9
Mounting Diameter (mm): 65
Type: Telecentric Lens
Primary Magnification PMAG: 0.15X
Maximum Sensor Format: 1/2"
Working Distance (mm): 169 - 265
Mount: C-Mount
Aperture (f/#): f/10
FOV @ Max Sensor Format, H x V (mm): 41.2 x 30.9
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View