

0.22 NA UV/VIS Patchcord 100 Micron Fiber w/ FC Connector



Stock #23-705 2 In Stock

-

1

+

S\$275<sup>.80</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | S\$275.80 each                |
| Qty 5-10       | S\$247.80 each                |
| Qty 11-24      | S\$221.20 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                   |
|----------------------------------|-------------------|
| Patchcord                        | Type:             |
| Multimode                        | Fiber Cable Type: |
| Physical & Mechanical Properties |                   |
| 1.5                              | Length (m):       |

|                                    |                             |
|------------------------------------|-----------------------------|
| 100                                | Core Diameter (µm):         |
| PVC MONOCOIL (0.112" OD)           | Jacket Material:            |
| Optical Properties                 |                             |
| Nylon                              | Coating Type:               |
| 0.22                               | Numerical Aperture NA:      |
| UV-VIS                             | Wavelength:                 |
| Hardware & Interface Connectivity  |                             |
| FC/PC                              | Connector:                  |
| Environmental & Durability Factors |                             |
| -40 to +100                        | Operating Temperature (°C): |
| Regulatory Compliance              |                             |
| Compliant                          | RoHS 2015:                  |
| View                               | Certificate of Conformance: |
| Compliant                          | Reach 250:                  |

## Product Details

- UV/MS and VIS/NIR Versions Available
- FC Connector Compatible with [Spatial Filters](#)
- FC Connector Compatible with [Fiber Alignment Mounts](#)
- FC and SMA Connector Options

High Quality Fiber Patchcords are designed for UV-VIS (190 - 1250nm) or VIS-NIR (300 - 2400nm) ranges. These Patchcords are 1.5 meters in length with Nylon or Tefzel coatings. With core diameters ranging from 50 – 1000µm, these patchcords provide quality solutions for a variety of core sizes. High Quality Fiber Patchcords are available with SMA905 or FC/PC connectors featuring a 0.22 numerical aperture. These Patchcords are ideal for applications requiring optimum transmission in the UV-VIS or VIS-IR wavelengths.

## Technical Information

