

0.3 OD M37.0 x 0.75, Mounted Absorptive ND Filter



Stock #59-165 3-5 DAYS

⊖ 1 ⊕

S\$62.35

ADD TO CART

Qty 1-9
S\$62.35
Qty 10+
S\$58.87
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
0.3

Clear Aperture CA (mm):
31.9

Filter Thread:
M37 x0.75

Substrate: ☐
ND Filter Glass

Thickness with Mount (mm): 4.50
Surface Quality: 80-50
Transmission (%): 50
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 5.2 ±0.3
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 39.0 ±0.3
Mount Thickness Including Threads (mm): 6.5

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View
