

0.3 OD M58.0 x 0.75, Mounted Absorptive ND Filter



Stock **#54-731** CLEARANCE CONTACT US

-

1

+

S\$56.48

ADD TO CART

Qty 1+
S\$56.48

Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
0.3

Clear Aperture CA (mm):
54.0

Filter Thread:
M58 x0.75

Substrate: ☐
ND Filter Glass

Thickness with Mount (mm):
5.00

Surface Quality: 80-50
Transmission (%): 50
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 3.8 ±0.1
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 60.0 +0/-0.2
Mount Thickness Including Threads (mm): 6.3

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View