

0.4 OD 25mm Dia, Absorptive ND Filter

See More by [Hoya](#)



Stock #46-213 3-5 DAYS

- 1 +

S\$63.80

ADD TO CART

Qty 1-10
S\$63.80
Qty 11+
S\$56.55
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00

Optical Density OD (Average):
0.4 ±0.05

Glass/Filter Number: Hoya ND-40
Substrate: ☐ ND Filter Glass
Coating: Uncoated
Index of Refraction n_d: 1.50
Surface Quality: 80-50
Transformation Temperature (°C): 525
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.5
Transmission (%): 40.0 (average)
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.1
Parallelism (mm): <0.02

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View