

TECHSPEC® 0.5 OD 12.5mm Dia UV-NIR ND Filter



UV-NIR Neutral Density Filters

Stock **#88-265** 3-5 DAYS

- 1 + **S\$181.25**

ADD TO CART

Qty 1-5

S\$181.25

Qty 6+

S\$162.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Optical Density OD (Average):
0.5

Substrate: [Fused Silica](#) (Corning 7980)

Coating: Metallic Based ND
Surface Quality: 40-20
Thickness (mm): 1.50 ±0.10
Transmission (%): 32.0
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 190 - 1700
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Optical Density Tolerance (%): ±10
Parallelism (arcsec): <5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View