

TECHSPEC[®] 0.6 OD 25mm Diameter, Reflective ND Filter



Stock #49-072 CLEARANCE 3-5 DAYS

-

1

+

S\$72.50

ADD TO CART

Qty 1-5
S\$72.50
Qty 6+
S\$58.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00

Angle of Incidence (°):
0

Optical Density OD (Average):
0.6

Substrate: Float Glass
Coating: Surface 1: Inconel
Reflection (%) : 37.00
Surface Quality: 80-50
Thickness (mm): 1.60 Nominal
Transmission (%) : 25.00
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.5
Clear Aperture (%) : 80
Neutrality: ±5% of Optical Density
Note: Optical density values are average over specified blocking wavelength range.
Surface Flatness (P-V): 4 - 6λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant