

0.6 OD M25.5 x 0.50, Mounted Absorptive ND Filter



Stock #59-168 CLEARANCE 3-5 DAYS

-

1

+

S\$46.33

ADD TO CART

Qty 1+

S\$46.33

Volume Pricing

[Request Quote](#)

Get Product Downloads

Optical Density OD (Average):
0.6

Clear Aperture CA (mm):
21.0

Filter Thread:
M25.5 x0.50

Substrate:
ND Filter Glass

Thickness with Mount (mm):
4.50

Surface Quality: 80-50
Transmission (%): 25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 5.2 ±0.3
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 27.5 ±0.3
Mount Thickness Including Threads (mm): 7

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View