

# 0.6 OD M39.0 x 0.50, Mounted Absorptive ND Filter



Stock **#59-171** 3-5 DAYS

- 1 +

**S\$62.35**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| <b>S\$62.35</b>               |
| Qty 10+                       |
| <b>S\$58.87</b>               |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

## Get Product Downloads

**Optical Density OD (Average):**  
0.6

**Clear Aperture CA (mm):**  
34.0

**Filter Thread:**  
M39 x0.50

**Substrate:** ☐  
ND Filter Glass

|                                                                       |
|-----------------------------------------------------------------------|
| <b>Thickness with Mount (mm):</b><br>5.00                             |
| <b>Surface Quality:</b><br>80-50                                      |
| <b>Transmission (%):</b><br>25                                        |
| <b>Type:</b><br>Mounted Imaging Filter                                |
| <b>Blocking Wavelength Range (nm):</b><br>400 - 700                   |
| <b>Mount Thickness (mm):</b><br>5.2 ±0.3                              |
| <b>Note:</b><br>AR Coating: MgF <sub>2</sub>                          |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤1.75% @400 - 700nm |
| <b>Mount Diameter (mm):</b><br>41.0 ±0.3                              |
| <b>Mount Thickness Including Threads (mm):</b><br>7                   |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>REACH 201:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---