

0.65X - 4.6X Dynamic Focus VZM™ Lens



Dynamic Focus VZM™ Lens

Stock **#89-999** CLEARANCE 3-5 DAYS

⊖ 1 ⊕

S\$2,112.58

ADD TO CART

Qty 1+
S\$2,112.58
Volume Pricing
Request Quote

Get Product Downloads

Length (mm): 248.00
Filter Thread: M22.5 x 0.50
Working Distance Tolerance (mm): ±3
Zoom Ratio: 7:1
Type: Zoom Lens

Primary Magnification PMAG: 0.65X - 4.6X
Maximum Sensor Format: 2/3"
Working Distance (mm): 87.00
Style: Liquid Lens
Lens Wavelength Range: VS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
