

0.66X Objective, 68mm WD

See More by [Infinity Photo-Optical Company](#)



InfiniTube FM-200 (1X), #58-310



Stock **#55-404** 2 In Stock

-

1

+

S\$392⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$392.00 each
Need More?	Request Quote

Product Downloads

General

Type:	
Lens Accessory	

Optical Properties

Primary Magnification PMAG:	
0.66X	
Working Distance (mm):	
68.00	

Sensor	
2/3"	Maximum Sensor Format:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:


Product Details

- Direct to Video C-Mount for 2/3" and Smaller Sensor Cameras
- Internal Focusing

InfiniTube™ FMSystems are used to mount infinite-conjugate objectives to C-mount cameras, yielding magnifications not possible with ordinary video lenses, such as 50X magnification. The InfiniTube™ system can be configured in a variety of fashions. It can be utilized alone (InfiniTube™ [#58-310](#) or [#58-309](#)) for applications where illumination is provided from another source such as a backlight or directional illumination. The InfiniTube™ FMSystems can also be configured for in-line illumination with attachments. The first in-line attachment ([#58-313](#)) has been designed for high performance with objectives having a magnification of 10X or below and is not suggested for use with higher magnification objectives. The second in-line attachment ([#58-312](#)) has been designed to work with increased efficiency when used with magnifications of 10X or higher, but can be utilized with all magnifications. All in-line attachments accept our [Fiber Optic Light Guides](#) with a 0.312" tip diameter.

Note: [Standard system](#) for 2/3" sensors still available.

Technical Information



System Includes	Stock No.
InfiniTube In-Line Assembly Unit	#58-311
Hitachi KP-D20B Camera	#55-837
15.1" Diagonal LCD Monitor (US version only)	#56-522
Y-C Cable (6 ft.)	#39-255
Mitutoyo/Achrovid™ Objective Adapter	#58-316
M-150 Fiber Optic Illuminator	#55-718
Fiber Optic Light Guide (48" L)	#39-367
Fiber Optic Adapter	#38-944
Standard Boom Stand	#54-120
Rack & Pinion Mounting Plate	#54-123
C-Clamp with 1/4-20 Mounting Hole	#57-788