

TECHSPEC® 0.75X MercuryTL™ Liquid Lens Telecentric Lens



0.75X MercuryTL™ Liquid Lens Telecentric Lens, #36-192



Stock **#36-192** 3-5 DAYS

− 1 +

S\$2,897.00

ADD TO CART

Qty 1+

S\$2,897.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length excluding Threads (mm):
148.70

Horizontal Field of View, 1/2" Sensor:
8.7mm

Horizontal Field of View, 2/3" Sensor:
11.7mm

Filter Thread:
M30.5 x0.50 (Female)

Weight (g): 222
Horizontal Field of View, 1/3" Sensor: 6.5mm
Stock No. of Mounting Clamp: #56-870 Sold Separately
Note: MercuryTL™
Typical Telecentricity @ 588nm (°): <0.057
Typical Distortion @ 588nm (%): <0.04
Mounting Diameter (mm): 36
Type: Telecentric Lens
Primary Magnification PMAQ: 0.75X
Maximum Sensor Format: 2/3"
Working Distance (mm): 85 - 99
Mount: C-Mount
Aperture (f/#): f/10
FOV @ Max Sensor Format, H x V (mm): 11.7 x 8.8
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View