

0.9 OD M46.0 x 0.75, Mounted Absorptive ND Filter



Stock #54-740 3-5 DAYS

- 1 +

S\$62.35

ADD TO CART

Qty 1-9
S\$62.35
Qty 10+
S\$57.27
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
0.9

Clear Aperture CA (mm):
42.0

Filter Thread:
M46 x0.75

Substrate: ☐
ND Filter Glass

Thickness with Mount (mm): 5.00
Surface Quality: 80-50
Transmission (%): 12.5
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 4.4 ±0.1
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 48.0 +0/-0.2
Mount Thickness Including Threads (mm): 6.4

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View