

1" Travel, 0.001" Grad. Mic. Drive S-Face



Drive Mechanisms

Stock **#33-733** **2 In Stock**

⊖ 1 ⊕ **\$142⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-9	\$142.80 each
Qty 10-24	\$128.52 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

Mitutoyo **Manufacturer:**

Physical & Mechanical Properties

1 **Travel (inches):**

Graduation (inches):

0.001	
10	Stem Diameter (mm):
Plain/Spherical	Stem/Spindle:
15	Stem Length (mm):
6.35	Spindle Diameter (mm):
27	Min. Spindle Length (mm):
18	Max. Diameter (mm):
95.5	Overall Length (mm):

Hardware & Interface Connectivity

English Micrometer	Type of Drive:
--------------------	-----------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
 - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential. Please reference individual product descriptions to see which stages are compatible with each drive mechanism.