

TECHSPEC® 10" Diameter x 100" FL Uncoated, Parabolic Mirror



Stock #35-726-000 3-5 DAYS

⊖ 1 ⊕ **\$3,004.40**

ADD TO CART

Qty 1-2
\$3,004.40

Qty 3+
\$2,553.45

Volume Pricing
[Request Quote](#)

Get Product Downloads

Substrate:
BOROFLOAT®

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:

N8

Diameter (inches):
10.00 +0.06/-0

Diameter (mm):
254.00 +1.5/-0

Effective Focal Length EFL (inches):
100.0

Effective Focal Length EFL (mm):
2,540.00

Radius of Curvature (mm):
5,080.00

Aperture (f#):
f/10

Coating:
Uncoated

Coating Type:
Metal

Back Surface:
Ground

Clear Aperture CA (mm):
229

Edge Thickness ET (inches):
1.75

Edge Thickness ET (mm):
44.50

Type:
Parabolic Mirror

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)
