

TECHSPEC®

10" Diameter x 60" FL Uncoated, Parabolic Mirror



Stock #32-274-000 

3-5 DAYS

-

1

+

S\$3,004.40

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-2                       |
| S\$3,004.40                   |
| Qty 3+                        |
| S\$2,553.45                   |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Substrate: 

BOROLOAT®

SUPREMAX®

Focal Length Tolerance (%):  
±1.5

Surface Quality:  
60-40

Surface Accuracy:  
λ/8

|                                                     |
|-----------------------------------------------------|
| <b>Diameter (inches):</b><br>10.0 +0.06/-0          |
| <b>Diameter (mm):</b><br>254.00 +1.5/-0             |
| <b>Effective Focal Length EFL (inches):</b><br>60.0 |
| <b>Effective Focal Length EFL (mm):</b><br>1,524.00 |
| <b>Radius of Curvature (mm):</b><br>3,048.00        |
| <b>Aperture (f/#):</b><br>f/6                       |
| <b>Coating:</b><br>Uncoated                         |
| <b>Coating Type:</b><br>Uncoated                    |
| <b>Back Surface:</b><br>Ground                      |
| <b>Clear Aperture CA (mm):</b><br>229               |
| <b>Edge Thickness ET (inches):</b><br>1.75          |
| <b>Edge Thickness ET (mm):</b><br>44.50             |
| <b>Type:</b><br>Parabolic Mirror                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |