


10 LED, Red Adjustable LED Bar Light



Stock **#34-878** 3-5 DAYS



1



S\$1,015.00

ADD TO CART

Qty 1+

S\$1,015.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red

Connector:
M12, 5 pins

Input Voltage (V):
24VDC

Model Number: EFFI-FLEX-10-625
Mount: 2 Rails (1 for M6 T-Nuts)
Operating Temperature (°C): -10 to 50
Dimensions (mm): 235.0 x 51.0 x 49.0
Wavelength (nm): 625.00
Power Supply: Power Supply Required and Sold Separately. USA: #15-874 Europe: #15-875 Japan: #15-874 Korea: #15-874 China: #15-874
Number of LEDs: 10.00
Type of Illumination: LED Illuminator
Geometry: Line Light
Illumination Mode: Strobed or Constant
Environmental Rating: IP40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View