

10 lp/mm, 1" x 3", Float Glass, Ronchi Ruling



Stock #38-258 CLEARANCE 4 In Stock

S\$265⁹³

ADD TO CART

Volume Pricing

Qty 1+	S\$265.93 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Length (inches):
3.00

Pattern Size (mm):
12.7 x 25.4

Thickness (mm):
1.10

Width (inches):
1.00

Optical Properties

Coating:

Vacuum Deposited Chrome

10.00 **Frequency (lp/mm):**

Float Glass **Substrate:**

3.00 **Optical Density OD (Average):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 240:**

Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.