

100 lp/mm, 1" x 3", Fused Silica, Ronchi Ruling



Stock #57-888 CLEARANCE CONTACT US

-
1
+
S\$606^{.20}

ADD TO CART

Volume Pricing

Qty 1-4	S\$606.20 each
Qty 5+	S\$576.24 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

3.00	Length (inches):
12.7 x 25.4	Pattern Size (mm):
1.10	Thickness (mm):
1.00	Width (inches):

Optical Properties

Vacuum Deposited Chrome **Coating:**

100.00 **Frequency (lp/mm):**

[Fused Silica](#) (Coming 7980) **Substrate:**

3.00 **Optical Density OD (Average):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.
