

100X Deluxe Illuminated Direct Measuring Microscope



Stock #55-679 8 In Stock

-

1

+

S\$777^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$777.00 each
Qty 5+	S\$738.64 each
Need More?	Request Quote

Product Downloads

General	
Type of Illumination:	Adjustable & removable, battery operated
Type of Focusing:	Rack and Pinion
Note:	Magnification includes 10XEyepiece
Physical & Mechanical Properties	
Field of View (mm):	1.8

0.01mm/0.001"	Increments:
200.00	Height (mm):
0 - 1.0	Reticle Scale (mm):
0 - 0.05	Reticle Scale (inches):
580.00	Weight (g):

Optical Properties

100X	Magnification:
5.5	Working Distance (mm):

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

Reticle cannot and should not be removed or replaced.

- 40X and 100X Models, Include 10X Eyepiece
- Inch/Metric Reticle
- Rack and Pinion Focusing

For quick and precise measurements in laboratories, workshops and assembly lines. Features a dual scale reticle graduated in both inches and millimeters. A turn of the eyepiece brings the reticle into sharp focus. Vertical adjustment knob sharpens the subject image. Includes a fully vertically adjustable battery operated penlight illuminator, which can be removed for use elsewhere. Scope has cutaway opening at base for subject manipulation.

Note: Reticle cannot and should not be removed or replaced.