

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Float Glass](#) / [4-6λ First Surface Mirrors](#)

[See all 61 Products in Family](#)

102 x 127mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#40-042** 3-5 DAYS

⊖ 1 ⊕ **S\$102.22**

ADD TO CART

Qty 1-5
S\$102.22
Qty 6+
S\$81.92
Volume Pricing
Request Quote

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm):

102.0 x 127.0 ±0.76
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 6.00
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 127.00
Width (mm): 102.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant