

1064nm 0 - 450mW, Fiber-Coupled Laser



Fiber-Coupled Laser System

Stock #62-698

CLEARANCE

CONTACT US

-

1

+

S\$5,072.03

ADD TO CART

Qty 1+
S\$5,072.03
Volume Pricing
Request Quote

Get Product Downloads



Operating Temperature (°C):
+10 to +30

Output Power (mW):
450 (Maximum)

Dimensions (mm):
76.2 L x 152.4 W x 254.0 H

Fiber Diameter (µm):
100

Wavelength (nm):
1,064.00

Weight (kg): 2.95
Wavelength Tolerance (nm): ±10
Operating Humidity: 5 to 95%, non-condensing
Modulation Frequency (kHz): DC-20, TTL
Length of Cable (m): 0.5
Beam Divergence (NA): 0.22, Nominal
Output Type: Fiber-Coupled
Type of Laser: Diode
Laser Class - CDRH: IIIb
Color: Infrared
Connector: SMA
Input Voltage (V): 100 - 240 AC
Bandwidth (nm): <3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View