

TECHSPEC[®] 10mm Diameter Enhanced Aluminum, λ/4 Mirror



Stock #45-598 ☐ In Stock

-

1

+

\$S\$72.50

ADD TO CART

Qty 1-5

\$S\$72.50

Qty 6+

\$S\$58.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
10.00

Surface Flatness (P-V):
λ/4

Substrate: ☐
[BOROFLOAT[®]](#)

Back Surface:

Commercial Polish
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 2.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant