

## 25mm Focal Length Lens, 1.1" Sensor Format



Compact Fixed Focal Length Lenses for 1.1" Sensors

Stock **#14-113** 3-5 DAYS

[Similar Products](#)



1



**S\$1,508.00**

ADD TO CART

Qty 1+

S\$1,508.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Iris Option:  
Variable

Length (mm):  
34.00

Filter Thread:  
M34 x0.50

Maximum Diameter (mm):  
39.5

Weight (g):

|                                                               |
|---------------------------------------------------------------|
| 78.6                                                          |
| <b>Maximum Image Circle (mm):</b><br>17.60                    |
| <b>Horizontal Field of View @ Max Sensor Format:</b><br>31.7° |
| <b>Horizontal Field of View, 1.1" Sensor:</b><br>31.7°        |
| <b>Type:</b><br>Fixed Focal Length Lens                       |
| <b>Focal Length FL (mm):</b><br>25.00                         |
| <b>Maximum Sensor Format:</b><br>1.1"                         |
| <b>Working Distance (mm):</b><br>300 - ∞                      |
| <b>Mount:</b><br>C-Mount                                      |
| <b>Aperture (f/#):</b><br>f/2.8 - f/16                        |
| <b>Distortion (%):</b><br>0.3                                 |
| <b>Lens Wavelength Range:</b><br>VIS                          |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Reach 224:</b><br><a href="#">Contains SVHC(s)</a>      |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |