

TECHSPEC® 1:1.5 with 20mm and 30mm EFL Achromats, 15mm Achromatic Pair



TECHSPEC Mounted Achromatic Lens Pairs

Stock **#43-997** [CONTACT US](#)



1



S\$264.63

ADD TO CART

Qty 1-5

S\$264.63

Qty 6+

S\$211.70

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
9.5

Center Air Spacing (mm):
1.90

Substrate: [S-BAH11](#) / [N-SF10](#) / [N-SSK8](#) / [N-SF10](#)

Surface Quality:

40-20
Working f#: f/3.13
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Effective Focal Length EFL A (mm): 20.00
Effective Focal Length EFL B (mm): 30.00
Housing Diameter (mm): 15 +0.0/-0.10
Housing Length (mm): 21 ±0.2
Lens Edge Spacing at Mount (mm): 4
Magnification: 1:1.5
Object Distance (mm): 12.90
Image Distance (mm): 22.06
Construction: Achromat Pair in Anodized Aluminum Housing
Type: Relay Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View