

TECHSPEC® 1:1.67 with 30mm and 50mm EFL Achromats, 30mm Achromatic Pair



TECHSPEC Mounted Achromatic Lens Pairs

Stock **#46-004** 3-5 DAYS

-

1

+

S\$329.15

ADD TO CART

Qty 1-5

S\$329.15

Qty 6+

S\$263.18

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
22.0

Center Air Spacing (mm):
2.12

Substrate: ☐
[N-BAF10](#) / [N-SF10](#) / [N-BAF10](#) / [N-SF10](#)

Surface Quality:

40-20
Working f#: f/2.16
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Effective Focal Length EFL A (mm): 30.00
Effective Focal Length EFL B (mm): 50.00
Housing Diameter (mm): 30 +0.0/-0.10
Housing Length (mm): 34 ±0.2
Lens Edge Spacing at Mount (mm): 8
Magnification: 1:1.67
Object Distance (mm): 19.19
Image Distance (mm): 39.68
Construction: Achromat Pair in Anodized Aluminum Housing
Type: Relay Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View