

1200 Grooves, 25mm Square, 400nm Ruled Diffraction Grating



Reflective Ruled Diffraction Gratings

Stock **#41-046** 3-5 DAYS

- 1 + **S\$194.30**

ADD TO CART

Qty 1+

S\$194.30

Volume Pricing

[Request Quote](#)

Get Product Downloads



Groove Density (grooves/mm):
1200

Blaze Wavelength (nm):
400

Blaze Angle (°):
13.88

Dimensions (mm):
25.0 x 25.0 ±0.5

Clear Aperture (%) : 90
Coating : Bare Aluminum
Construction : Ruled Grating
Direction of Grooves : Parallel to Short Dimension
Length (mm) : 25.00
Substrate : ☐ Float Glass
Thickness (mm) : 9.50 ±0.5
Type : Reflective Diffraction Grating
Width (mm) : 25.00
Alignment of Grooves to Edge (°) : ±0.5
Absolute Peak Efficiency, Typical (%) : 73
Peak Efficiency Avg, Typical (%) : >68

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View
