

1200 Grooves/mm, 50mm Square, UV Holographic Grating



Reflective Holographic Gratings

Stock #43-214 3-5 DAYS



1



S\$522.00

ADD TO CART

Qty 1+

S\$522.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Groove Density (grooves/mm):
1200

Wavelength Range (nm):
250 - 400

Dimensions (mm):
50.0 x 50.0 ±0.5

Coating:
Bare Aluminum

Construction: Holographic Grating
Length (mm): 50.00
Substrate:  Float Glass
Thickness (mm): 9.50 ±0.5
Type: Reflective Diffraction Grating
Wavelength: UV
Width (mm): 50.00
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%): 74
Peak Efficiency Avg, Typical (%): >69

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
