

TECHSPEC® 12.5/12.7mm Diameter Rotation Kinematic Mount, 2-Screws



12.5/12.7mm Diameter Rotation Kinematic Mount, 2-Screws, #36-637

Stock **#36-637** 3-5 DAYS

⊖ 1 ⊕ **S\$221.85**

ADD TO CART

Qty 1-4
S\$221.85
Qty 5+
S\$199.66
Volume Pricing
Request Quote

Get Product Downloads



Type:
Adjustable - Rotary & Tip-Tilt

Type of Optics:
Circular

Size of Compatible Optics (mm):
12.5 - 12.7

Number of Adjustment Screws: 2
Clear Aperture CA (mm): 10.0
Travel (mm): No Z-Axis Translation
Coarse Rotation (°): 360
Construction: Aluminum plates, stainless steel screws, and brass thread bushings
Angle Tolerance (°): 0.4 per 0.25mm turn
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 4
Thermal Stability (μrad): <5
Adjustment Screw Pitch (mm): 0.25
Compatible Post: M4 x0.7, 8-32
Min. Thickness of Compatible Optics (mm): 1.8
Pointing Stability (μrad): 1.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant