

TECHSPEC® 12.5" Diameter x 75" FL Uncoated, Parabolic Mirror



Stock **#32-276-000** 3-5 DAYS

⊖ 1 ⊕ **\$S\$4,154.25**

ADD TO CART

Qty 1-2
\$S\$4,154.25
Qty 3+
\$S\$3,530.75
Volume Pricing
Request Quote

Get Product Downloads

Substrate: □
[BOROFLOAT®](#)[SUPREMAX®](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 12.5 +0.06/-0
Diameter (mm): 317.50 +1.5/-0
Effective Focal Length EFL (inches): 75.0
Effective Focal Length EFL (mm): 1,905.00
Radius of Curvature (mm): 3,810.00
Aperture (f/#): f/6
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Clear Aperture CA (mm): 286
Edge Thickness ET (inches): 2.13
Edge Thickness ET (mm): 54.10
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View