

1.25", White, High Intensity Pattern Projecting Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity Pattern Projecting Spot Lights

Stock **#18-638** 3-5 DAYS

⊖ 1 ⊕

S\$1,400.70

ADD TO CART

Qty 1+

S\$1,400.70

Volume Pricing

[Request Quote](#)

Get Product Downloads

Color:
White

Diameter (inches):
1.25

Model Number:
SL256-WH11C

Operating Temperature (°C):
0 - 50

Weight (g):

413
Diameter of Compatible Reticle (mm): 20.8
LED Lifetime (hours): 50000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Length of Cable (m): 2
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Constant
Environmental Rating: IP50
Minimum Input Current: 0.794

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
