

TECHSPEC[®] 12.5/12.7mm Diameter, T-Mount Thick Optic Mount



Stock #52-954 4 In Stock

-

1

+

S\$97⁸²

ADD TO CART

Volume Pricing	
Qty 1-4	S\$97.82 each
Qty 5-9	S\$87.07 each
Qty 10-25	S\$80.50 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type: Fixed

Circular	Type of Optics:
Optic Mount (Fixed)	Function:
Physical & Mechanical Properties	
21.5	Extension Length (mm):
Black Anodized Aluminum (6061 T6)	Construction:
24.95	Total Length (mm):
48.0	Outer Diameter (mm):
11.50	Clear Aperture CA (mm):
15.50	Max. Thickness of Compatible Optics (mm):
5.00	Min. Thickness of Compatible Optics (mm):
Threading & Mounting	
12.5 - 12.7	Diameter of Compatible Optics (mm):
T-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

PRODUCT DETAILS

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

Note: [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

TECHNICAL INFORMATION

T-Thread Achromat / Thick Lens Mount

