

TECHSPEC® 12.5mm Dia. x 2mm Thick, Uncoated, Ge Window



Germanium (Ge) Windows

Stock **#68-735** 3-5 DAYS

⊖ 1 ⊕ **S\$330.60**

ADD TO CART

Qty 1-10

S\$330.60

Qty 11+

S\$297.61

Volume Pricing

[Request Quote](#)

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
90.00

Clear Aperture CA (mm):
11.25

Diameter (mm): 12.50 +0.0/-0.1
Thickness (mm): 2.00 ±0.1
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 6.1
Density (g/cm³): 5.33
Edges: Fine Ground
Index of Refraction n_d: 4.002 @ 11µm
Knoop Hardness (kg/mm²): 780
Parallelism (arcmin): <1
Poisson's Ratio: 0.28
Substrate: Germanium (Ge)
Surface Flatness (P-V): λ/10 @ 10.6µm
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 2000 - 14000
Young's Modulus (GPa): 102.7

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View