

12.5mm Diameter, 70R/30T, Plate Beamsplitter



Stock #45-314 3-5 DAYS

- 1 +

S\$68.15

ADD TO CART

Qty 1-9
S\$68.15
Qty 10+
S\$47.85
Volume Pricing
Request Quote

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: AR 1/4λ MgF₂ @ 550nm

Construction:
Plate

Diameter (mm):
12.50

Dimensional Tolerance (mm): ±0.38
Edges: Cut
Reflection/Transmission Ratio (R/T): 70/30
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 1.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant